


Ecosoft MO6TI5

Reverse Osmosis System

Piping and Instrumentation Diagram



**PIPES**

- (01)— PVC pipe 63 mm O.D.
- (02)— PVC pipe 50 mm O.D.
- (03)— PVC pipe 32 mm O.D.
- (04)— PE hose 1¼" O.D.
- ≡(05)≡ Stainless steel pipe DN25
- ≡(06)≡ Stainless steel pipe DN50

**VALVES**

- Ball Valve
- Globe Valve
- Regulating Valve
- Check Valve



Motorized Valve

**INSTRUMENTS**

- Pressure gauge (panel mount)
- Pressure switch (panel mount)
- Rotameter
- Conductivity probe (process mount)